



# Connection cable TPS-MVP-TC80, 0.5 m

# Connection cable



## Connection cable TPS-MVP-TC80, 0.5 m

- Connection to TC 80 with D-Sub 15-pin male, outgoing cable 90° and blocking diode
- Interface connection RS-485/M12 and two M8 accessory ports
- Connection to MVP with D-Sub 15-pin male
- Length: TPS-MVP 0.5 m / MVP-TC 80 0.5 m
- Blocking diode prevents current from flowing back to the TPS when the pump is operated in generator mode

### Technical Data

Technical Data	Connection cable TPS-MVP-TC80, 0.5 m
Electronic drive unit	TC 80
Cable length	0.5 m

### Order number

Order number	Connection cable TPS-MVP-TC80, 0.5 m
Connection cable TPS-MVP-TC80, 0.5 m	PM 071 775 -T



Are you looking for an optimum vacuum solution?

Talk to us:

Pfeiffer Vacuum GmbH

Germany

T +49 6441 802-0

Or scan the barcode, to visit our web page:



<https://webportal.pfeiffer-vacuum.com/global/en/contact>



Errors and/or changes excepted. - 11/1/2024

Follow Us On Social Media  
#pfeiffervacuum



[www.pfeiffer-vacuum.com](http://www.pfeiffer-vacuum.com)

