



# External oil filter DE 2, 230 V

---




Illustration only

## External oil filter DE 2, 230 V, 50 Hz

- For Pascal, DuoLine™, UnoLine Plus
- The external oil filter is operated in the oil circuit of rotary vane pumps
- DE 2 Filter includes 2 cartridges. Factory supply is an activated alumina and a cellulose cartridge
- Furthermore, cartridges with cellulose and activated charcoal are available
- Application activated alumina: Mineral acids, Lewis acids, polar media
- Standard factory installed cartridges are activated alumina
- Applications activated charcoal: Chlorine and chlorinated media, nitrous vapor, ammonia
- Replacement cartridge cellulose (for USA): Order number: 12633
- Customer benefits: Longer service life of the operating fluid, longer pump lifetime
- Applications cellulose: Filtration of particles from operating fluid

# External oil filter DE 2, 230 V

## Dimensions



Technical Data	External oil filter DE 2, 230 V, 50 Hz
Factory installed cartridge	Activated alumina and cellulose
Input voltage(s)	230 V AC, 50/60 Hz
Capacity	1.8 l
Weight	17 kg

Order number	External oil filter DE 2, 230 V, 50 Hz
External oil filter DE 2, 230 V, 50 Hz	104374



Errors and/or changes excepted. - 9/30/2025

**Are you looking for an optimum vacuum solution?**

**Talk to us:  
Pfeiffer Vacuum GmbH  
Germany  
T +49 6441 802-0**

**Or scan the barcode, to visit our web page:**



<https://webportal.pfeiffer-vacuum.com/global/en/contact>

**Follow Us On Social Media  
#pfeiffervacuum**



[www.pfeiffer-vacuum.com](http://www.pfeiffer-vacuum.com)

**PFEIFFER** 