



# Mounting kit for HiPace® 60/80




Illustration only

**Mounting kit for HiPace 60/80, DN 63 ISO-K, including coated centering ring with integrated protection screen and claw grips**

- For DN 63 ISO-K
- Suitable for HiPace 60/80 and SplitFlow 50
- Centering ring with multi-functional coating for anti-twist protection and integrated protection screen
- Protective screen: to safeguard against foreign objects, mesh width 4 mm, molecular conductance for N<sub>2</sub> 303 l/s
- 4 x claws M8
- Note: Required for secure mounting of the turbopump

| Technical Data                           | Mounting kit for HiPace 60/80, DN 63 ISO-K, including coated centering ring with integrated protection screen and claw grips |
|--|--|
| Number of lugs                           | 4 pcs.   |
| Molecular conductance for N <sub>2</sub> | 303 l/s  |
| Connection flange                        | DN 63 ISO-K  |

| Order number   | Mounting kit for HiPace 60/80, DN 63 ISO-K, including coated centering ring with integrated protection screen and claw grips |
|--|--|
| Mounting kit for HiPace 60/80, DN 63 ISO-K, including coated centering ring with integrated protection screen and claw grips | PM 016 512 -T  |



Errors and/or changes excepted. - 2/21/2025

**Are you looking for an optimum vacuum solution?**

**Talk to us:**

**Pfeiffer Vacuum GmbH**

**Germany**

**T +49 6441 802-0**

**Or scan the barcode, to visit our web page:**



<https://webportal.pfeiffer-vacuum.com/global/en/contact>

**Follow Us On Social Media**

**#pfeiffervacuum**



[www.pfeiffer-vacuum.com](http://www.pfeiffer-vacuum.com)

**PFEIFFER** 